

405nm Violet Light Laser-B200mW




FIGURE 1

The 405nm UV laser adopts imported UV LD, which has the characteristics of high brightness, high modulation frequency, and pure spectrum. It is suitable for scientific research, ultraviolet light communication, medicine, food hygiene and other fields.

The light source is controlled by a touch screen, which can easily set parameters such as output power, frequency, and duty cycle. At the same time, for the convenience of use, the light source also provides an external control interface. Customers can use the TTL modulation port to synchronize the light-on and off-time of the laser with the external control signal. A key switch on the front panel ensures that only authorized personnel can access the light source.

In addition, for different applications, we can provide customized services such as divergence angle and control method. For details, please contact our engineers.

Specifications	
Model	BDT-B405-MW200
Wavelength	405nm
Wavelength deviation	+/-10nm
Output Power	0~200mW
Power stability	3%
Fiber parameters	105um, 0.22NA
Fiber optic connector	SMA905 or FC/PC
Fiber length	2.5米 m



Power display	percentage
Setting accuracy	0.1%
Adjustment range	~0 % to 100%
Supply voltage	230 VAC 50 - 60 Hz (115 VAC optional)
Cooling method	Air cooling
Dimensions (mm)	See "Laser Outline Drawing"
Operating temperature	0 to 40 °C(Higher or lower operating temperature can be customized)
Storage temperature	-20 to 80 °C
Life expectancy	10000 hour
Warranty	1 year




FIGURE 2 Laser shape diagram